



Plastic hood with integrated cable gland

Features

- Construction height reduced by 25 % when compared to the existing standard solution
- Large range of cable diameters (9 - 17 mm) can be used
- Reduced logistical effort due to integrated cable gland
- Also available as variant with glued seal for Han-Brid® inserts

Technical characteristics

Material	Plastic
Locking element	Plastic
Protection degree acc. to DIN EN 60 529 in locked position	IP 65 / 67
Cable diameter	9 - 17 mm

Identification

Part-Number

Size

Drawing

Dimensions in mm

Hood Han® 3 A

with integrated cable gland

without glued seal

with glued seal for Han-Brid® inserts

19 20 003 0410

3 A

19 20 003 0413

3 A

