



Ha-VIS preLink® HIFF RJ45 AP Box

Advantages

- Flexible, suitable for on-wall mounting or for top-hat mounting rail (35mm)
- Economical, time-saving installation due to the use of pre-assembled data cables with Ha-VIS preLink® termination
- Robust design, powder-coated steel plate housing
- Future proof, Cat. 6 Class E_A 500 MHz transmission performance, transmission rate up to 10 Gbit/s

Applications

- Structured cabling for industrial premises
- IP 20 installation

Identification

Ha-VIS preLink® HIFF RJ45 AP Box
RJ45 wall-mounted box, consisting of:


- 1x steel-plate housing, 2-parts
- 2x Ha-VIS preLink® Set, RJ45 jack HIFF, AWG 22/23
- 2x grommet with membrane
- 1x assembly instruction

Number of ports: 2
Cable diameter: max. Ø 9 mm
Mounting: on-wall or DIN Rail
Dimensions (WxHxD): 60 x 81 x 70 mm
Degree of protection: IP 20
Operating temperature: -40°C ... +70°C
Housing material: steel plate
Colour: RAL 7016 (anthracite grey)

Part number

20 82 101 0220

Drawing



Dimensions in mm

Accessory, optional:
DIN Rail mounting bracket

20 80 000 0003

