



Hood, high construction

Features

- High construction, therefore large cabling space
- M25 cable entry
- Suitable for harsh environments
- Highly EMC resistant
- Suitable for sensitive interconnections that have to be protected and shielded
- Captive locking screws

Technical characteristics

Material	Zinc die-cast
Surface	Epoxy powder paint, RAL 9005 (black) RoHS conform Black chrome plated: not RoHS conform
Locking element	
- screw locking	M4
- material	Stainless steel
- tightening torque	2 Nm
Limiting temperatures	-40 °C ... +125 °C
Protection degree acc. to DIN EN 60 529 in locked position	IP 68

Identification	Part-Number	Size	Drawing	Dimensions in mm
----------------	-------------	------	---------	------------------

Hood Han® 3 HPR

high construction

black chrome plated

19 40 003 0411

3 A

epoxy powder paint

19 40 703 0411

3 A

